




DON'T LET A BATTERY STOP YOU

### Specifications

со	MPATIBILITY	All Cadex Universal Battery Adapters are reverse and forward compatible with all Cadex analyzers. Please reference Analyzer specifications for further information.	ELECTRICAL	16kb non-volatile memory. Battery settings (C-Code) are entered through the analyzer. The battery parameters are stored in the adapter. Each Cadex UBA holds 10 unique C-Codes.
ME	CHANICAL	SnapLock™ Design, interchangeable with custom battery adapters.	BATTERY TYPES	Lithium Ion/Polymer (Li-ion), Nickel Metal Hydride (NiMH), Nickel Cadmium (NiCd), Lead Acid (SLA).
со	NTACTS	RigidArm: Gold plated contacts*, rated at 3A FlexArm: Gold plated contacts*, rated at 3A SmartCable: Two alligators, red and black, connceted by banana plugs; rated at 3A SmartConnect with FlexStrip*: micro-connector for select iPhone/Samsung batteries, rated at 3A * Field replaceable	WARRANTY	Cadex warrants against defective materials and workmanship for 1 year from purchase date. (2 years when purchased with a Cadex anayzer)



Cadex Electronics, Inc. Visit **cadex.com/adapters** for more information Enquiries: **info@cadex.com** 

@cadexelectronics



cadex.com/adapters











Narrow and awkwardly

placed battery contacts



## **Smart**Connect

Some smartphones have non-removable batteries, but these also need testing. The SmartConnect with FlexStrip enables testing without removing the battery. With device opened, unplug the battery cable from the phone socket and insert it into the matching socket on the FlexStrip. Part #: 07-111-6150

**Rigid**Arm<sup>™</sup>

The 4-wire RigidArm<sup>™</sup>, spring-loaded arms lock into position for repetitive testing. A retractable floor holds batteries vertically or horizontally. Simple cable connections offer easy polarity selection, and temperature sensor ensure safe operation. Part #: 07-110-0192



The Smart Cable features 4-wire battery cables with alligator clips to provide easy connection to larger batteries. Ideal for batteries with exposed tabs or special terminals. The insulated alligator clops are connected to your Cadex analyzer by banana plugs. A magnetized temperature sensor is included. Part #: 07-110-0115

**Flex**Arm™

The FlexArm<sup>™</sup> features battery contacts on flexible, spring-loaded arms to reach narrow and awkwardly placed battery contacts. Magnetic guides on the insulated steel floor hold the battery in any position. Banana plugs enable easy polarity selection. A spring-loaded temperature sensor is embedded in the floor.

#### Part #: 07-110-0180







CHOOSE ANY ANALYZER

# **C5100B** STOREFRONT ANALYZER



### **C7X00** PROFESSIONAL ANALYZER More at cadex.com/c7



C8000 LAB ANALYZER More at cadex.com/c8



Not what you're looking for? We have also a selection of over 3,200 different custom-made adapters for almost any battery type. Or inquire with us to develop your own. Learn more at cadex.com/adapters

